


# **NSHD** CONNECTOR



#### 1.0 mm pitch/Disconnectable Crimp style connectors



In 1.0 mm pitch and dual-row secure lock type connector, this NSHD connector realizes a top grade of a space saving in the industry and supports a high densification of equipment.

- Excellent mounting and dismounting workability of socket
- Adopting large lock in consideration of unlocking and withstanding external force
- Various lineups of circuits
- An existing crimping applicator is available.

#### Specifications -

• Current rating: 1.0 A AC/DC (AWG #28)

Voltage rating: 50 V AC/DC

Temperature range: -25°C to +85°C

(including temperature rise in applying

electrical current)

• Contact resistance: Initial value/ 20 mΩ max.

After environmental tests/ 40 m $\Omega$  max.


• Insulation resistance: 100  $M\Omega$  min.

• Withstanding voltage: 500 VAC/minute


 Applicable wire: Conductor size/ AWG #32 to #28 Insulation O.D./ 0.4 to 0.8 mm


- \* In using the products, refer to "Handling Precautions for Terminals and Connectors" described on our website (Technical documents of Product information page).
- \* RoHS2 compliance
- \* Dimensional unit: mm
- \* Contact JST for details.

#### PC board layout and Assembly layout




(16, 20, 24, 28, 32 circuits)






Side entry type



(Mating side faces to this side)

(16, 20, 24, 28, 32 circuits)

(40 circuits)




Note: 1. The above figure is the figure viewed from the connector mounting side.

 $2.\ Tolerances\ are\ non-cumulative: \pm\ 0.05\ mm\ for\ all\ centers.\ The\ dimensions\ above\ should\ serve\ as\ a\ guideline.\ Contact\ JST\ for\ details.$ 

## **NSHD CONNECTOR**

#### Contact



Madel No	Applicable wire		Insulation O.D.	Q'ty/	
Model No.	mm <sup>2</sup>	AWG #	(mm)	reel	
SNSHD-003T-P0.2	0.032~0.08	32~28	0.4~0.8	23,000	

#### Material and Finish


Copper alloy, tin-plated (reflow treatment)

#### RoHS2 compliance

Contact	Crimping		Applicator	
Contact	machine	Crimp applicator	Dies	Crimp applicator with dies
SNSHD-003T-P0.2	AP-K2N	MKS-L-10-3	MK/SSH/L-003-02	APLMK SSH/L003-02

Note: 1. Contact JST for applicable wires in case that it is not usable due to wire size. 2. Contact JST for fully automatic crimping applicator.

#### Housing



No. of	Model No.	Dimension	Q'ty/	
circuits		Α	В	bag
16	NSHDR-16V-Z	7.0	9.2	2,500
20	NSHDR-20V-Z	9.0	11.2	2,000
24	NSHDR-24V-Z	11.0	13.2	1,500
28	NSHDR-28V-Z	13.0	15.2	1,000
32	NSHDR-32V-1-Z	15.0	17.2	1,000
40	NSHDR-40V-2-Z	19.0	21.2	900

#### Material and Finish

PBT, UL94V-0, ivory

#### RoHS2 compliance

<For reference> As the color identification, the following alphabet shall be put in the underlined part.

For availability, delivery and minimum order quantity, contact JST.


Z...ivory TR...tomato red E...blue MG...moss green DPK...dark pink

#### NSHD CONNECTOR


#### Shrouded header


### Top entry type

<16 circuits>





#### <20, 24, 28 circuits>







#### <32 circuits>






#### <40 circuits>







#### Side entry type


<16 circuits>







#### <20, 24, 28 circuits>







#### <32 circuits>





#### <40 circuits>





#### Top entry type

No. of	Model No.	Dimensions (mm)			Q'ty/
circuits		Α	В	С	reel
16	BM16B-NSHDZS-TFT	7.0	10.2	8.8	1,600
20	BM20B-NSHDZS-TFT	9.0	12.2	10.8	1,600
24	BM24B-NSHDZS-TFT	11.0	14.2	12.8	1,600
28	BM28B-NSHDZS-TFT	13.0	16.2	14.8	1,600
32	BM32B-NSHDZS-1-TFT	15.0	18.2	16.8	1,600
40	BM40B-NSHDZS-1-TFT	19.0	22.2	20.8	1,600

#### Material and Finish

Contact: Copper alloy, copper-undercoated, tin-plated (reflow treatment) Header: Polyamide resin, UL94V-0, ivory
Reinforcing tab: Copper alloy, copper-undercoated, tin-plated (reflow treatment)

#### RoHS2 compliance

Note: These products listed above are supplied on embossed-tape.

As the color identification,

the following alphabet shall be put in the underlined part. For availability, delivery and minimum order quantity, contact JST.

#### BM16B-NSHDZS-TFT

Z...ivory TR...tomato red E...blue MG...moss green DPK...dark pink

#### Side entry type

		, ,,,				
ı	No. of	Madel No	Dimensions (mm)		(mm)	Q'ty/
	circuits	Model No.	Α	В	С	reel
	16	SM16B-NSHDZS-TF	7.0	10.2	8.8	1,000
	20	SM20B-NSHDZS-TF	9.0	12.2	10.8	1,000
	24	SM24B-NSHDZS-TF	11.0	14.2	12.8	1,000
	28	SM28B-NSHDZS-TF	13.0	16.2	14.8	1,000
	32	SM32B-NSHDZS-1-TF	15.0	18.2	16.8	1,000
	40	SM40B-NSHDZS-1-TF	19.0	22.2	20.8	1,000

#### Material and Finish

Contact: Copper alloy, copper-undercoated, tin-plated (reflow treatment) Header: Polyamide resin, UL94V-0, ivory

Reinforcing tab: Copper alloy, copper-undercoated, tin-plated (reflow treatment)

#### RoHS2 compliance

Note: These products listed above are supplied on embossed-tape.

<For reference> As the color identification,

the following alphabet shall be put in the underlined part. For availability, delivery and minimum order quantity, contact JST.

#### SM16B-NSHDZS-TF

Z...ivory TR...tomato red E...blue MG...moss green DPK...dark pink