






1.5mm pitch/Disconnectable Insulation displacement and Crimp style connectors



The SMT top entry type headers that can be mated with the 1.5 mm pitch CZ connector socket are on the lineup.

- Suction tape is not required because the flat area for picking up is provided to the connector.
- This header can be accommodated to both the crimp style and the insulation displacement (ID) style sockets.

Specifications -

	CZF / CZ connectors	CZF / CZH connectors			
Current rating	2 A AC, DC (AWG #26)				
Voltage rating	100V AC, DC				
Temperature rise	-25°C to +85°C (including temperature rise in applying electrical current)				
Contact resistance					
Insulation resistance					
Withstanding voltage					
	UL10272 (Contact JST for other UL style wires.)				
	AWG #28, # 26				
Applicable wire	Conductor / 7-strands, tincoated annealed copper Insulation O.D. / 0.7 to 0.83 mm	AWG #28 to # 26			

* Refer to "General Instruction and Notice when using

Terminals and Connectors" at the end of this catalog.


* Contact JST for details.


* Compliant with RoHS.

Standards -

Recognized E60389

PC board layout and Assembly layout






Note: 1. The above figure is the figure viewed from the connector mounting side.

2. Tolerances are non-cumulative: ±0.05 mm for all centers. The dimensions above should serve as a guideline. Contact JST for details.

CZF CONNECTOR

CZF connector SMT type header




Circuits	Model No.	Dimensio	Q'ty/		
	Model No.	А	В	reel	
2	BM02B-CZFKS-TF	1.5	6.0	1,150	
3	BM03B-CZFKS-TF	3.0	7.5	1,150	
4	BM04B-CZFKS-TF	4.5	9.0	1,150	
5	BM05B-CZFKS-TF	6.0	10.5	1,150	
6	BM06B-CZFKS-TF	7.5	12.0	1,150	
8	BM08B-CZFKS-TF	10.5	15.0	1,150	
Material and Finish					


Pin: Copper alloy, copper-undercoated, tin-plated (reflow treatment) Wafer: Polyamide, UL94V-0, black

RoHS compliance This product displays (LF)(SN) on a label.

CZ connector socket



CZH connector contact



Model No.	Applicable wire		Insulation O.D. (mm)	O'ty/rool	
woder No.	mm ²	AWG#		Qity/ieei	
SCZH-002T-P0.5	0.08~ 0.13	28~26	0.8~1.1	13,000	


Material and Finish

Phosphor bronze, tin-plated (reflow treatment)

RoHS compliance

.	Crimping	Applicator			
Contact	machine	Crimp applicator	Dies	Crimp applicator with dies	
SCZH-002T-P0.5		MKS-L	MK/SCZH-002-05	APLMK SCZH002-05	
3020-0021-20.5	AF-NZIN	—	—	—	

CZH connector housing



Circuits	Model No.	Dimensions (mm)			Q'ty/
Circuits		Α	В	С	box
2	CZHR-02V-S	1.5	4.5	3.5	1,000
3	CZHR-03V-S	3.0	6.0	5.0	1,000
4	CZHR-04V-S	4.5	7.5	6.5	1,000
5	CZHR-05V-S	6.0	9.0	8.0	1,000
6	CZHR-06V-S	7.5	10.5	9.5	1,000
8	CZHR-08V-S	10.5	13.5	12.5	1,000
Material					

PBT, UL94V-0, natural (white)

RoHS compliance

<For reference> As the color identification,

the following alphabet shall be put in the underlined part.

For availability, delivery and minimum order quantity, contact JST.

ex. CZHR-02V-S

S...natural (white) K...black H...gray Y...yellow

