

HSF

NOTES:
 Current Rating: 2.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 500V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40℃ to +105℃
 Contact Material: Copper Alloy
 Contact Plating: Au Over Ni
 Insulator Material: High Temperature Thermoplastic(UL94V-0)

Ordering Information

2293 - 4 XX S XX C Y N X 6

No. of Pins per ROW: 02-40PIN

Contact Plating:

G1=3u"Gold
 G3=10u"Gold
 G4=15u"Gold
 S1=Sel.3u"Gold/Tin
 S3=Sel.10u"Gold/Tin
 S4=Sel.15u"Gold/Tin

Insulator

C=PA9T

Packing:





T=Tube

A=Tray

Contact Plating	Test Point M	Test Point N
G1	3U"	1U"
G3	10U"	1U"
G4	15U"	1U"
S1	3U"	120U"
S3	10U"	120U"
S4	15U"	120U"

Item	Pitch	Mating
Standard	2.00	1215/1220
Alternate		

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	FIT	PART NO.
				x.x ±0.40	Surong Xu	2019/12/06	UNIT	mm	2293-4XXSXXCYNX6
A1	2019/12/06	MODIFY DRAWING	-----	x.xx ±0.25	CHECK	DATE	SIZE	A4	TITLE: 2.00*2.00mm PC104 Plus FOUR ROW 180°DIP H=9.35 DIP=2.30
AO	2016/11/21	NEW	-----	x.xxx ±0.15	APPROVE	DATE	SHEET	1/1	Customer NO.
				Angle ± 3°			PROJ.		
				DIM TOL					

WCON
 Http: www.wcon.com

WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com

WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: salesks@wcon.com