



HSF

NOTES:

Rated Current:3.0AMP.
 Contact Resistance:20mΩ Max.
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min.
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Au or Sn Over Ni
 Insulator Material:PA9T+33%G.F UL94V-0 BK



Recommended P.C.B Layout (Top Side)
 (PCB BOARD TOLERANCE±0.05)



Ordering Information

1125-22 XX XX M XXX C R XX Δ 2

No. of Pins Per Row: 02-40
 Contact Plating: G0=Gold Flash, G3=10u"Gold, G4=15u"Gold, G5=30u"Gold, S0=Gold Flash/Tin, S3=10u"Gold/Tin, S4=15u"Gold/Tin, S5=30u"Gold/Tin, SN=Tin, SM=Matte Tin
 Pin Length: L=B+C+D+ $\frac{W-2.54}{2}$ Standard:
 Insulator Material: C=PA9T
 Packing: T=Tube, P=Tube+CAP, R=Tape & Reel+CAP
 Series No. 01-99



Item	Pin Length	W	D	B	E	Mating
Standard	---	7.50	0.60	6.00	---	2171 2185
Alternate						

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	Fit	PART NO.
A2	2018/01/22	Modify P/N	Δ 2	x.x ±0.40	Ruipeng	2018/01/22	UNIT	mm	1125-22XXXXMXXXC RXX
A1	2012/10/31	Modify Drawing	-----	x.xx ±0.25	CHECK	DATE	SIZE	A4	TITLE:
A0	2012/05/28	NEW	-----	x.xxx ±0.15	APPROVE	DATE	SHEET	1/1	PH2.54 DUAL ROW DOUBLE PLASTIC SMT H=2.5
				Angle ± 3'			PROJ.		Customer NO.
				DIM TOL					

WCON
 Http: www.wcon.com

WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com

WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: salesks@wcon.com