


HSF

NOTES:
 Rated Current:3.0AMP
 Contact Resistance:20mΩ max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ min
 Operation Temperature:-25°C to +85°C

Insulator Material:PBT+30%G.F UL94V-0
 Use with:WF2543-T
 Mated with:WF2543-Wafer



Specification & Ordering Information:

Circuit	Part No.	Dimension	
		A	$\triangle A/B$
1x01	WF2543-1H01X01		2.54
1x02	WF2543-1H02X01	2.54	5.08
1x03	WF2543-1H03X01	5.08	7.62
1x04	WF2543-1H04X01	7.62	10.16
1x05	WF2543-1H05X01	10.16	12.7
1x06	WF2543-1H06X01	12.70	15.24
1x07	WF2543-1H07X01	15.24	17.78
1x08	WF2543-1H08X01	17.78	20.32
1x09	WF2543-1H09X01	20.32	22.86
1x10	WF2543-1H10X01	22.86	25.40
1x11	WF2543-1H11X01	25.40	27.94
1x12	WF2543-1H12X01	27.94	30.48
1x13	WF2543-1H13X01	30.48	33.02
1x14	WF2543-1H14X01	33.02	35.56
1x15	WF2543-1H15X01	35.56	38.10
1x16	WF2543-1H16X01	38.10	40.64
1x17	WF2543-1H17X01	40.64	43.18
1x18	WF2543-1H18X01	43.18	45.72
1x19	WF2543-1H19X01	45.72	48.26
1x20	WF2543-1H20X01	48.26	50.80

Ordering Information


WF2543 -1 H XX X 01



No.of pins
01P~20P

Color
W=White
B=Black

Packing
0=PE Bag



REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	FIT	PART NO.
A2	2013/01/14	MODIFY PART NO.	—	OPERATION	JYHuang	2013/01/14	UNIT	mm	SEE TAB
A2	2012/12/28	MODIFY PART NO.	—	x.X			in		
A1	2012/11/19	MODIFY DIM "B"	—	x.XX	CHECK	DATE	SIZE	A4	TITLE:
AO	2012/09/08	NEW	—	x.XXX	APPROVE	DATE	SHEET	1/1	SINGLE ROW 2.54 HOUSING
				Angle			PROJ.		Customer NO.
				± 3'					
				DIM	TOL				

WCON

Http: www.wcon.com

WCON-Dongguan
 Tel: +86 769 85358920
 Fax: +86 769 85358915
 E-mail: sales@wcon.com

WCON-Kunshan
 Tel: +86 512 57468408
 Fax: +86 512 57468468
 E-mail: salesks@wcon.com