




HSF

NOTES:
 Rated Current: 3.0AMP.
 Rating Voltage: 250V AC/DC
 Contact Resistance: 20mΩ Max.
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ Min.
 Operation Temperature: -40℃ to +105℃
 Contact Material: Brass
 Contact Plating: Au or Sn Over Ni
 Insulator Material: PA9T+33%G.F UL94V-0 BK

Recommended P.C.B Layout (Top Side)
 (PCB BOARD TOLERANCE ±0.05)



Ordering Information

1125-11 XX XX R XXX C 0 XX

No. of Pins: 02-40
Contact Plating: G0=Gold Flash, G3=10u"Gold, G4=15u"Gold, G5=30u"Gold, S0=Gold Flash/Tin, S3=10u"Gold/Tin, S4=15u"Gold/Tin, S5=30u"Gold/Tin, SN=Tin, SM=Matte Tin
Pin Length: L=A+B+D+3.75, Standard: 110=11.0, 140=14.0, 148=14.8
Insulator Material: C=PA9T
Packing: 0=PE Bag, T=Tube
Series No.: 01-99

Item	Pin Length	A	E	B	Mating
Standard	11.00	3.00	4.02	3.00	2135
	14.00	3.00	4.02	6.00	2171 2185
	14.80	3.00	4.82	6.00	2171 2185
Alternate					

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	Fit	PART NO.
A2	2018/06/02	Cancel PBT & Modify P/N	A2	x.x ±0.40	Surong Xu	2018/06/02	UNIT	mm	1125-11XXXXRXXXCOXX A1 A2
A1	2018/01/22	Modify P/N	A1	x.xx ±0.25	CHECK	DATE	SIZE	A4	TITLE: PH2.54 SINGLE ROW 90° CONCAVE BENDING H=2.5
A0	2012/05/17	NEW	----	x.xxx ±0.15	APPROVE	DATE	SHEET	1/1	Customer NO.
				Angle ± 3'			PROJ.		

WCON
 Http: www.wcon.com
 WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com
 WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: salesks@wcon.com