



HSF

NOTES:
 Current Rating: 3.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C

Contact Material: Phosphor Bronze Or Brass
 Contact plating: Au Or Sn over Ni
 Insulator Material: PA9T+33%G.F UL94V-0(Std)
 Or PBT+30%G.F UL94V-0

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Ordering Information

2185 - 1 XX S XX X Y N X X

No. of Pins per ROW: 02-40PIN
 Contact Plating: G0=Gold Flash, G3=10μ"Gold, G4=15μ"Gold, G5=30μ"Gold, S0=Gold Flash/Tin, S3=10μ"Gold/Tin, S4=15μ"Gold/Tin, S5=30μ"Gold/Tin, SN=Tin, SM=Matte Tin
 Insulator: A=PBT, C=PA9T
 Packing: T=Tube, A=Tray, R=Tape&Reel+Cap
 Series No.:

Item	Pitch	Mating
Standard	2.54	1115/1120/1125
Alternate		

Dimension antitheses list	
ITEM	DIM A
Standard	3.15
Alternate	

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	FIT	PART NO.
A2	2017/02/28	ADD Tape Packing&Cap	A2	x.x ±0.40	Surong Xu	2017/02/28	UNIT	mm	2185-1XXSXXXYNXX
A1	2016/08/23	ADD THE DIM.	A1	x.xx ±0.25	CHECK	DATE	SIZE	A4	TITLE:
AO	2012/08/15	NEW	---	x.xxx ±0.15	APPROVE	DATE	SHEET	1/1	FH2.54mm SINGLE ROW 180°DIP H=8.50
				Angle ± 3'			PROJ.	φ	Customer NO.
				DIM TOL					

WCON

Http: www.wcon.com

WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com
 WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: sales@wcon.com