




# HSF

NOTES:  
 Rated Current:3.0AMP.  
 Rating Voltage:250V AC/DC  
 Contact Resistance:20mΩ Max.  
 Withstand Voltage:1000V AC/DC  
 Insulation Resistance:1000MΩ Min.  
 Operation Temperature:-25℃ to +85℃

Insulator Material:PA66 UL94V-0  
 Use with:WF2541-T  
 Mated with:WF2541-Wafer



## Ordering Information

WF2541 - H XX X 0 1

No. of Pins: 02-16P  
 Colour: E= Beige 0= PE Bag  
 Packing

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW JYHuang	DATE 2013/09/02	SCALE	FIT	PART NO. WF2541-HXXX01
				X.X	±0.40					
A1	2013/09/02	MODIFY THE DIM	—	X.XX	±0.25	CHECK	DATE	UNIT mm	A4	TITLE: "M" TYPE 2.54mm Housing
AO	2012/09/07	NEW	—	X.XXX	±0.15	APPROVE	DATE	SHEET 1/1		Customer NO.
				Angle DIM	± 3' TOL			PROJ.		

**WCON**  
 Http: www.wcon.com

WCON-Dongguan      WCON-Kunshan  
 Tel: +86 769 85358920      Tel: +86 512 57468408  
 Fax: +86 769 85358915      Fax: +86 512 57468468  
 E-mail: sales@wcon.com      E-mail: salesks@wcon.com