


HSF

NOTES:

Current Rating: 2.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 500V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40℃ to +125℃(Au)
 -40℃ to +105℃(Sn)
 Contact Material: Phosphor Bronze
 Contact plating: Au Or Sn over Ni
 Insulator Material: PA9T+33%GF UL94V-0



Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)




Ordering Information

2227T-2 XX M XX CUN X X


No. of Pins per Row: 02-40Pin
 Contact Plating: G0=Gold Flash, G3=10μ"Gold, G4=15μ"Gold, G5=30μ"Gold, SN=Tin
 Packing: T=Tube, P=Tube+CAP, R=Tape&Reel+CAP
 Series No. 1=Type 1, 2=Type 2



2*2P~2*4P



TYPE 1 W/O POST



TYPE 2 WITH POST

SECTION A-A

Item	Pitch	Mating
Standard	2.00	1215/1220
Alternate		

PIN	2-15P	16-25P	26-40P
M	0.10	0.15	0.18

TITLE	PART NO.
TYPE 1	2227T-2XXMXXCUNX1
TYPE 2	2227T-2XXMXXCUNX2

OPERATION	DRAW	DATE	SCALE	FIT	PART NO.
x.x ±0.40	XSR	2019/01/16	UNIT mm		SEE TABLE
x.xx ±0.25	CHECK	DATE	SIZE A4		TITLE: FH2.00mm DUAL ROW 180°SMT H=2.7
x.xxx ±0.15			SHEET 1/1		Customer NO.
Angle ± 3°	APPROVE	DATE	PROJ.		
DIM TOL					

WCON
 Http: www.wcon.com

WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com

WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: salesks@wcon.com