

# HSF

**NOTES:**

Current Rating: 3.0AMP  
 Contact Resistance: 20mΩ Max  
 Withstand Voltage: 1000V AC/DC  
 Insulation Resistance: 1000MΩ Min  
 Operation Temperature: -40°C to +105°C

Contact Material: Phosphor Bronze  
 Contact plating: Au Or Sn over Ni  
 Insulator Material: PA9T+30%G.F UL94V-0

## Ordering Information

2157 - 1 XX S XX CYN A 1



No. of Pins per Row: 02-40PIN  
 Contact Plating:  
 G0=Gold Flash  
 G3=100"Gold  
 G4=15μ"Gold  
 G5=30μ"Gold  
 S0=Gold Flash/Tin  
 S3=10μ"Gold/Tin  
 S4=15μ"Gold/Tin  
 S5=30μ"Gold/Tin  
 SN=Tin  
 SM=Matte Tin

Packaging:  
 T=Tube  
 A=Tray

Item	Pitch	Mating
Standard	2.54	1115/1120/1125
Alternate		

REV	DATE	MODIFICATION DESCRIPTION
A0	2012/08/10	NEW

OPERATION	DRAW	DATE	SCALE	FIT	PART NO.
XX	JYHuang	2012/08/10	UNIT	mm	2157-1XXSXXCYNX1
XX	CHECK	DATE	SIZE	A4	TITLE:
X.XXX	±0.25		1/1		PH2.54 SINGLE ROW 180° DIP H=5.7
Angle	±0.15	DATE	SHEET	1/1	Customer NO.
± 3'			PROJ.		
APPROVE					



# WCON

Http: www.wcon.com  
 WCON-Dongguan  
 Tel: +86 769 85358920  
 Fax: +86 769 85358915  
 E-mail: sales@wcon.com  
 WCON-Kunshan  
 Tel: +86 512 57468408  
 Fax: +86 512 57468468  
 E-mail: sales@wcon.com