



HSF

NOTES:

Current Rating: 2.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 500V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40℃ to +105℃(SN)
 -40℃ to +125℃(AU)

Contact Material: Phosphor Bronze
 Contact plating: Au Or Sn over Ni
 Insulator Material: LCP+30%GF UL94V-0

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Ordering Information


2263 - 2 XX S XX D Y N T 5

No. of Pins per ROW: 02-40PIN

Contact Plating:
 G0=Gold Flash
 G3=10μ"Gold
 G4=15μ"Gold
 G5=30μ"Gold
 S0=Gold Flash/Tin
 S3=10μ"Gold/Tin
 S4=15μ"Gold/Tin
 S5=30μ"Gold/Tin
 SN=Tin
 SM=Matte Tin

Insulator:
 D=LCP

Packing:
 T=Tube



SECTION A-A

Item	Pitch	DIM A	Mating
Standard	2.00	2.2	1215/1220
Alternate			

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW	DATE	SCALE	FIT	PART NO.
				DIM	TOL					
A0	2019/05/10	NEW	-----	x.x	±0.40	CHECK	DATE	UNIT	mm	2263-2XXSXXDYNT5
				x.xx	±0.25	APPROVE	DATE	SIZE	A4	TITLE: FH2.00mm DUAL ROW 180°DIP H=6.35 DIP=2.2
				x.xxx	±0.15		DATE	SHEET	1/1	Customer NO.
				Angle	± 3'			PROJ.	☉	

WCON
 Http: www.wcon.com

WCON-Dongguan WCON-Kunshan
 Tel: +86 769 85358920 Tel: +86 512 57468408
 Fax: +86 769 85358915 Fax: +86 512 57468468
 E-mail: sales@wcon.com E-mail: salesks@wcon.com