



HSF

NOTES:
 Current Rating: 1.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 500V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C

Contact Material: Phosphor Bronze
 Contact plating: Au Or Sn over Ni
 Insulator Material: PA9T+33%GF UL94V-0

Recommended P.C.B Layout (Top Side)
 (PCB BOARD TOLERANCE ±0.05)



Ordering Information


2357-1 XX M XX CUN X X

No. of Pins per Row: 02-50Pin

Contact Plating:
 G0=Gold Flash
 G3=10μm Gold
 G4=15μm Gold
 G5=30μm Gold
 S0=Gold Flash/Tin
 S3=10μm Gold/Tin
 S4=15μm Gold/Tin
 S5=30μm Gold/Tin
 SN=Tin

Packing:
 T=Tube
 P=Tube+CAP
 R=Tape&Reel+CAP

Series No.
 1=Type 1
 2=Type 2



Item	Pitch	Mating
Standard	1.27	1310/1315/1320
Alternate		

TITLE	PART NO.
TYPE 1	2357-1XXMXXCUNX1
TYPE 2	2357-1XXMXXCUNX2

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW	DATE	SCALE	FIT	PART NO.
				x.x	±0.40					
A1	2018/05/05	MODIFY P/N ; ADD DIM.	-----	x.xx	±0.25	CHECK	DATE	SIZE	A4	SEE TABLE
A0	2012/07/10	NEW	-----	x.xxx	±0.15	APPROVE	DATE	SHEET	1/1	TITLE: FH1.27mm SINGLE Row 180°SMT H=5.70
				Angle	± 3°			PROJ.	⌀	Customer NO.
				DIM	TOL					

WCON

Http: www.wcon.com

WCON-Dongguan
 Tel: +86 769 85358920
 Fax: +86 769 85358915
 E-mail: sales@wcon.com

WCON-Kunshan
 Tel: +86 512 57468408
 Fax: +86 512 57468468
 E-mail: salesks@wcon.com