

HSF


NOTES:

- Rated Current: 7.0AMP
- Contact Resistance: 30mΩ max
- Withstand Voltage: 1000V AC/DC
- Insulation Resistance: 1000MΩ min
- Operation Temperature: -40℃ to +105℃
- Contact Material: Phosphor Bronze
- Contact Plating: Sn Over Ni
- Insulator Material: LCP+30%G.F UL94V-0

Ordering Information

2989-1XX M XX D UN T 1

No. of Pins per Row: 02-20Pin
 Contact Plating: SN=Tin, SM=Matte Tin
 Packing: T=Tube, P=Tube+CAP, R=Tube&Reel+CAP



Recommended P.C.B Layout (Top Side)
 (PCB BOARD TOLERANCE±0.05)

SECTION "A-A"

Item	Pitch	Mating
Standard	5.08	1925
Alternate		

A2	2017/06/08	Modify	OPERATION	±0.40	DRAW	Surong Xu	DATE	2017/06/08	SCALE	UNIT	FIT	PART NO.	2989-1XXMXXDUNT1
A1	2013/06/17	Modify GAP 4.30→3.80	X.XX	±0.25	CHECK		DATE		mm	A4		TITLE:	FH5.08 SINGLE SMT H=8.9
A0	2012/07/14	NEW	X.XXX	±0.15	APPROVE		DATE		SHEET	1/1		Customer NO.	
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL				PROJ.				

WCON

Http: www.wcon.com
 WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com
 WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: sales@wcon.com