

# HSF

**NOTES:**





- Rated Current: 3.0AMP
- Contact Resistance: 20mΩ max
- Withstand Voltage: 1000V AC/DC
- Insulation Resistance: 1000MΩ min
- Operation Temperature: -40°C to +105°C
- Contact Material: Phosphor Bronze
- Contact Plating: Au Over Ni
- Insulator Material: PA9T+30%G.F UL94V-0

## Ordering Information

2135 - 1 XX S XX CUNT 2

- No. of Pins per ROW: 02-40PIN
- Contact Plating:  
 G0=Gold Flash  
 G3=10μ"Gold  
 G4=15μ"Gold  
 G5=30μ"Gold  
 S0=Gold Flash/Tin  
 S3=10μ"Gold/Tin  
 S4=15μ"Gold/Tin  
 S5=30μ"Gold/Tin  
 SN=Tin  
 SM= Matte Tin

Item	Pitch	Mating
Standard	2.54	1115/1120/1125
Alternate		



REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	APPROVE	DATE	SCALE	FIT	PART NO.
A0	2012/08/02	NEW		Angle	± 3°			SHEET	1/1	Customer NO.

OPERATION	DRAW	DATE	SCALE	FIT	PART NO.
XX	JYHuang	2012/08/02	mm		2135-1XXXXXCUNT2
XX	CHECK	DATE	UNIT		
X.XXX			A4		
X.XXX			SIZE		
Angle			SHEET		
			1/1		
			PROJ.		

TITLE:	PH2.54mm SINGLE ROW 180° DIP
H=3.5	

# WCON

Http: www.wcon.com

WCON-Dongguan  
 Tel: +86 769 85358920  
 Fax: +86 769 85358915  
 E-mail: sales@wcon.com

WCON-Kunshan  
 Tel: +86 512 57468408  
 Fax: +86 512 57468468  
 E-mail: sales@wcon.com