











# HSF

NOTES:  
 Current Rating: 1AMP  
 Contact Resistance: 35mΩ max  
 Withstand Voltage: 500V AC/DC  
 Insulation Resistance: 1000MΩ min  
 Operation Temperature: -55℃ to +105℃

Contact Material: Phosphor Bronze  
 Contact plating: Au or Sn over Ni  
 Shell Material: SPCC, t=0.50mm  
 Housing Material: PBT+30%GF(UL94V-0)  
 Cover Material: LCP+30%GF(UL94V-0)



PART NO.	PIN	A	E	F	G
6320M-014SSXXMNA01	14P	7.62	13.81	18.19	17.14
6320M-020SSXXMNA01	20P	11.43	17.62	22.00	20.95
6320M-026SSXXMNA01	26P	15.24	21.43	25.81	24.76
6320M-036SSXXMNA01	36P	21.59	27.78	32.16	31.11
6320M-040SSXXMNA01	40P	24.13	30.32	34.70	33.65
6320M-050SSXXMNA01	50P	30.48	36.67	41.05	40.00
6320M-068SSXXMNA01	68P	41.91	48.10	52.48	51.43
6320M-080SSXXMNA01	80P	49.53	55.72	60.10	59.05
6320M-100SSXXMNA01	100P	62.23	68.42	72.80	71.75



## Ordering Information

6320M- XXX S S XX M N A 01

No. of Pins: Contact Plated:  
 014=14P S1=3u" Gold /Tin  
 020=20P S2=5u" Gold /Tin  
 026=26P S3=10u" Gold /Tin  
 036=36P S4=15u" Gold /Tin  
 040=40P S5=30u" Gold /Tin  
 050=50P  
 068=68P  
 080=80P  
 100=100P

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW XSR	DATE	SCALE	FIT	PART NO.
A1	2019/09/20	MODIFY	—	X.X ±0.40	XSR	2019/09/20	UNIT	mm	6320M-XXXSSXXMNA01
A0	2019/06/06	NEW	—	X.XX ±0.25	CHECK	DATE	SIZE	A4	TITLE:
				X.XXX ±0.15	APPROVE	DATE	SHEET	1/1	1.27mm MDR SCSI Male (Soldering Type)
				Angle ± 3'			PROJ.	Customer NO.	
				DIM TOL					

**WCON**  
 Http: www.wcon.com  
 WCON-Dongguan Tel: +86 769 85358920  
 WCON-Kunshan Tel: +86 512 57468408  
 Fax: +86 769 85358915  
 Fax: +86 512 57468468  
 E-mail: sales@wcon.com  
 E-mail: sales@wcon.com