

HSF

NOTES:

Rated Current: 3.0AMP

Contact Resistance: 30mΩ max

Withstand Voltage: 500V AC/DC

Insulation Resistance: 1000MΩ min

Operation Temperature: -25℃ to +85℃

Contact Material: Phosphor Bronze

Contact Plating: Sn over Ni

Wire Range: AWG#26~#30

Ordering Information


WF2005 - T P SN 0 2

Material:

P=Phosphor Bronze

Contact Plating:

SN=Tin



				OPERATION		DRAW Wan.Bo	DATE 2018.8.15	SCALE	1:1	PART NO. WF2005-TPSN02	<div>WCON</div> <div>Http: www.wcon.com</div> <div>WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com</div> <div>WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: sales@wcon.com</div>	
				X.X	±0.40			UNIT	<div>mm</div> <div>inch</div>			
				X.XX	±0.25	CHECK	DATE	SIZE	A4	TITLE:		
				X.XXX	±0.15					2.00mm Pitch WTB CONNECTOR		
A0	2018.8.15	NEW	-	Angle	± 3°	APPROVE	DATE	SHEET	1/1	Customer NO.		
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL			PROJ.				

A0

2018.8.15

NEW

-