

两脚落差不能超过0.04



GT-TC018A-H035-L1

G-SWITCH

Operating Force



A=160gf
B=250gf

Switch Height (mm)

H034=3.4mm
H035=3.5mm
H0375=3.75mm



Switch lifetime (Force)

L05=50,000 Cycles
L1=100,000 Cycles



P.C.B LAND DIMENSION

Circuit Diagram



G-Switch Specification:

Operating temperature range: -30°C to +85°C
 Rating: 50mA.12V DC
 Insulation resistance: 100MΩ min.100V DC
 Dielectric strength: 250V AC for 1 min
 Contact resistance: 100m Ω max.
 Travel: 0.15±0.05mm



G-Switch Electronic (HongKong) CO.,Ltd.

Unless otherwise specified, Tolerance:
 X. ±0.30
 X.x ±0.20
 X.xx ±0.15
 X.xxx ±0.10
 Angles ±3°

DESIGN FengFengChen DATE 2019.05.29
 CHECKED DATE
 APPROVED DATE
<http://www.dg-switch.com>
 TEL:0769-82388879

Molde code:
 GT-TC018A-H035-L1
 REV.: X1 SCALE: 4:1 UNIT: mm
 SIZE: A4 SHEET: 1/1