


P.C.B Layout (copper-sided view)



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

Model NO	PJ-2110-A	PJ-2110-B
Schematic		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.																																																																																				
	A		NEW																																																																																							
<table border="1"> <tr> <td>② Terminal</td> <td></td> <td>4</td> <td>Phosphor bronze</td> <td>Au Plating</td> <td></td> <td></td> </tr> <tr> <td>① Housing</td> <td></td> <td>1</td> <td>Nylon</td> <td>Black</td> <td></td> <td></td> </tr> <tr> <td>ITEM</td> <td>PART NAME</td> <td>TER'NO.</td> <td>QTY.</td> <td>MATERIAL</td> <td>FINISHING</td> <td>REMARK</td> </tr> <tr> <td colspan="2">APPROVALS</td> <td colspan="2">DATE</td> <td colspan="3">TITLE: PHONE JACKES</td> </tr> <tr> <td colspan="2">DRAWN</td> <td colspan="2">J.X.Zhang</td> <td colspan="3">2013/11/11</td> </tr> <tr> <td colspan="2">CHECKED</td> <td colspan="2"></td> <td colspan="3">PART NO. PJ-2110</td> </tr> <tr> <td colspan="2">APPROVALS</td> <td colspan="2"></td> <td colspan="3">SCALE: 1:1</td> </tr> <tr> <td colspan="2">TOLERANCES ARE</td> <td colspan="2">30~0.15</td> <td colspan="2">±0.30</td> <td>PROJ-4</td> </tr> <tr> <td colspan="2"></td> <td colspan="2">10~0.30</td> <td colspan="2">±0.20</td> <td>ANGLE</td> </tr> <tr> <td colspan="2"></td> <td colspan="2">5~10</td> <td colspan="2">±0.15</td> <td>UNIT: mm</td> </tr> <tr> <td colspan="2"></td> <td colspan="2">~5</td> <td colspan="2">±0.10</td> <td>DRAWING NO.</td> </tr> <tr> <td colspan="2"></td> <td colspan="2"></td> <td colspan="2">±2'</td> <td>SHEET 1 OF 1</td> </tr> </table>							② Terminal		4	Phosphor bronze	Au Plating			① Housing		1	Nylon	Black			ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK	APPROVALS		DATE		TITLE: PHONE JACKES			DRAWN		J.X.Zhang		2013/11/11			CHECKED				PART NO. PJ-2110			APPROVALS				SCALE: 1:1			TOLERANCES ARE		30~0.15		±0.30		PROJ-4			10~0.30		±0.20		ANGLE			5~10		±0.15		UNIT: mm			~5		±0.10		DRAWING NO.					±2'		SHEET 1 OF 1
② Terminal		4	Phosphor bronze	Au Plating																																																																																						
① Housing		1	Nylon	Black																																																																																						
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK																																																																																				
APPROVALS		DATE		TITLE: PHONE JACKES																																																																																						
DRAWN		J.X.Zhang		2013/11/11																																																																																						
CHECKED				PART NO. PJ-2110																																																																																						
APPROVALS				SCALE: 1:1																																																																																						
TOLERANCES ARE		30~0.15		±0.30		PROJ-4																																																																																				
		10~0.30		±0.20		ANGLE																																																																																				
		5~10		±0.15		UNIT: mm																																																																																				
		~5		±0.10		DRAWING NO.																																																																																				
				±2'		SHEET 1 OF 1																																																																																				
<p>HAQI ELECTRONICS CO.,LTD</p>																																																																																										