



P.C.B LAYOUT(Copper-side view)



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

②	Terminal	3	Phosphor bronze	Au Plating			
①	Housing	1	Nylon	Black			
ITEM	PART NAME	TERN.O.	QTY.	MATERIAL	FINISHING	REMARK	
APPROVALS		DATE					
DRAWN		J.X.Zhang					
CHECKED		2013/11/11					
APPROVALS		TITLE: PHONE JACKES					
APPROVALS		PART NO. DC-023					
TOLERANCES ARE		30 ^{±0.15}	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ. SHEET 1 OF 1
ECON. NO.		REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
NEW							

HPQ
 ELECTRONICS CO.,LTD