


Rating:0.5A 30V DC  
 Contact Resistance:100 mΩ Max.  
 Operating temperature:−20℃~70℃  
 Operating force:3–20N  
 Operating Life:5,000cycles

P.C.B Layout (Pattern Side)



ITEM	PART NAME	TERN.O.	QTY.	MATERIAL	FINISHING	REMARK
③	Spring	—	1	SUS	SI Plating	—
②	Terminal	—	2	Phosphor bronze	Au Plating	—
①	Housing	—	1	Nylon	Black	—

APPROVALS	DATE	TITLE:
DRAWN J.X.Zhang	2013/11/11	PHONE JACKETS
CHECKED		DC-0605

APPROVALS	PART NO.	SCALE:	PROJ.
TOLERANCES ARE	DC-0605	1:1	PROJ. SHEET 1 OF 1
30 <sup>±0.15</sup>			
10 <sup>±0.20</sup>			
5 <sup>±0.15</sup>			
~ 5			
±Z'			

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	B		NEW			
	A					



ELECTRONICS CO.,LTD