



P.C.B LAYOUT(Copper-side view)



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3~20N
 Operating Life:5,000cycles

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

② Terminal	2	Phosphor bronze	Au Plating
① Housing	1	Nylon	Black
ITEM	PART NAME	TERN.O.	QTY.
APPROVALS		DATE	
DRAWN	J.X.Zhang	2013/11/11	
CHECKED			
APPROVALS			
TOLERANCES ARE		30 ^{±0.15}	±0.30
	10 ^{±0.30}	±0.20	±0.15
	5 ^{±0.10}	±0.15	±0.10
	~ 5	±0.10	±0.10
TITLE:		PHONE JACKES	
PART NO.		DC-060	
SCALE:		1:1	
DRAWING NO.		PROJ. SHEET 1 OF 1	

HRONICS
 ELECTRONICS CO.,LTD