


P.C.B Layout (copper-sided view)



Rating:0.5A 30V DC  
 Contact Resistance:100 mΩ Max. △  
 Operating temperature: -40°C~+80°C  
 Operating force:3-20N  
 Operating Life:5,000cycles

Model NO	PJ-327A-A	PJ-327A-B
Schematic		
	PJ-327A-D	PJ-327A-E

△

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	B		NEW			
	A					

② Terminal	5	Phosphor bronze	Au Plating
① Housing	1	Nylon	Black
ITEM	PART NAME	TER.NO.	QTY.
APPROVALS		DATE	
DRAWN	J.X.Zhang	2013/11/11	
CHECKED		TITLE:	PHONE JACKETS
APPROVALS		PART NO.	PJ-327A
TOLEFRANCES ARE		SCALE:	1:1
30~0.11	±0.30	ANGLE	
10~0.30	±0.20	UNIT:	mm
5~10	±0.15	SCALE:	1:1
~5	±0.10	DRAWING NO.	
DRAWN		DATE	
CHECKED		TITLE:	PHONE JACKETS
APPROVALS		PART NO.	PJ-327A
TOLEFRANCES ARE		SCALE:	1:1
30~0.11	±0.30	ANGLE	
10~0.30	±0.20	UNIT:	mm
5~10	±0.15	SCALE:	1:1
~5	±0.10	DRAWING NO.	

**HPD**  
 ELECTRONICS CO.,LTD