



P.C.B Layout (copper-sided View)



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

ECN NO.	REV.	DATE.	DESCRIPTION.	CHECK.	APPRO.
	A		NEW		

② Terminal	5	Phosphor bronze	Au Plating
① Housing	1	Nylon	Black
ITEM	PART NAME	TER.NO.	QTY.
APPROVALS	DATE		
DRAWN	J.X.Zhang	2013/11/11	
TITLE: PHONE JACKES			
PART NO. P.J-381			
ELECTRONICS CO.,LTD			
SCALE: 1:1			
UNIT: mm			
DRAWING NO.			
SHEET 1 OF 1			

CHECKED	APPROVALS	TOLERANCES ARE	30 ^{+0.15} / _{-0.10}	±0.30	ANGLE	±2°	PROJ.
		5 ^{+0.15} / _{-0.10}	±0.15	±2°			