


额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	160±30gf 250±50gf
寿命试验 Operating Life	100,000 cycles 70,000 cycles
行程 Travels	0.25±0.1mm



NO.	Name	Number	Qty	Material	Remarks
⑤	Terminal	4		Brass	Silvering
④	Reed	1		Phosphorus copper	Silver covered
③	Base	1		PPA	Black
②	Cover	1		SPCC	Nickel Plating
①	Keystoke	1		PPA	Black

0~3	±0.05	±0.10	±0.20
>3~6	±0.05	±0.10	±0.30
>6~30	±0.10	±0.20	±0.50
>30~120	±0.15	±0.30	±0.80
未注尺寸公差 (mm)			

第一视角 	设计	图面	A4	东莞市美韩电子科技有限公司 Dongguan Usakro Electronic Technology Co., Ltd.			
	Jack Jin	单位	MM				
	审核	比例		1:1	DWG NO.	型号: UK-B0219-TP-160	SIZE
	Jacky Zhong	重量		1/1	PART NO.	规格: 6*6*7.3方头 贴片	A4
	批准	页码	1/1	1 of 1			VER
	Tony Meng	版次	A/0				R