




HSF


NOTES:
 Current Rating: 3.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40℃ to +105℃

Contact Material: Brass
 Contact plating: Au over Ni
 Insulator Material: PA9T+33%G.F UL94V-0


Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Mating With 2171
SMT TYPE WITH BUMP



Mating With 2185
DIP TYPE WITHOUT BUMP



Ordering Information

3110A-XX S XX B K00 X X

- No. of Pins: 02-80P
- Contact Plating: G0=Gold Flash, G3=10u"Gold, G4=15u"Gold, G5=30u"Gold, S0=Gold Flash/Tin, S3=10u"Gold/Tin, S4=15u"Gold/Tin, S5=30u"Gold/Tin, SN=Tin
- Color Insulator: B=Black, G=Gray(427C)
- Packing: A=Tray, T=Tube

Dimension antitheses list		
NO. Pin	STANDARD(A)	L
6P-8P	3.3mm	4.00
10P-80P		4.40

PART NO.	"WCON" LOGO
3110A-XXSXXBKXXXX	无
3110A-XXSXXBKXXXXW	有

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	FIT	PART NO.
				x.x ±0.40	Ding	2019/02/15	UNIT	mm	3110A-XXSXXBKXXXX
				x.xx ±0.25	CHECK	DATE	SIZE	A4	TITLE:
				x.xxx ±0.15	APPROVE	DATE	SHEET	1/1	2.54 BOX HEADER 180° H=8.95
				Angle ± 3°			PROJ.	Customer NO.	
				DIM TOL					



Http: www.wcon.com

WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com	WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: salesks@wcon.com
---	--