



备注:

1. 适用电线(Wire Range):#16(1.5MM<sup>2</sup>)
2. 端子材质(Terminal Body):紫铜(Copper)
3. 塑胶材质(Insulation)/颜色(Color):Nylon 94V-2/French-Black German-Red
4. 表面处理(Plating):镀锡(Tin)
5. 图纸上标有★为关键尺寸, ☆为重要尺寸
6. 未注尺寸公差为±0.2
7. 符合ROHS2.0和REACH标准

模具编号	Item No. 料号	mm主要尺寸				
		L±0.5	F±0.3	W±0.2	D±0.1	C±0.1
EVN15	EVN1508-N	14.5	8	3.7	2.1	1.8
EVN15	EVN1510-N	16.5	10			
EVN15	EVN1512-N	18.5	12			
EVN15	EVN1518-N	24.5	18			

A0 VER	MODIFICATION	DRAW	DATE	TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.	SHEET	1/1			
				X.	±0.30	X°	±5°		CHKD	DATE	2010.4.12		
				.X	±0.20	.X°	±2°		APPD	PRODUCT NAME	欧式端子		
				.XX	±0.08	.XX°	±1°		VIEW	PART. NO.	EVN15系列	UNITS	mm
				.XXX	±0.03	.XXX°	±0.5°					SCALE	1:1