


P.C.B LAYOUT MOUNTING PATTERN

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	160±30gf ▶ 250±50gf
寿命试验 Operating Life	100,000 cycles 70,000 cycles
行程 Travels	0.25±0.1mm

9.0
8.0
7.0
6.5
6.0
5.0
4.3
▶ 3.8
高度/(mm)



CIRCUIT DIAGRAM

┌	盖板	铁厚0.3	1	——
┌	按钮	PPA黑	1	——
└	弹片	进口不锈钢覆银	1	——
└	基座	PPA黑	1	——
└	卡件	黄铜厚0.3	1	——
项目	名称	材质	数量	表面处理

>0.5~2	±0.05	±0.10	±0.15
>2~5	±0.15	±0.20	±0.25
>5~10	±0.25	±0.28	±0.30
角度 ANGLE	±0.5°		
未注尺寸公差(mm)			

第一视角 ☉	设计 Jack Jin	图面 单位	A4 MM
	审核 Jacky Zhong	比例 重量	
	批准	页码	1/1
	Tony Meng	版次	A/0

东莞市美韩电子科技有限公司 Dongguan Usakro Electronic Technology Co., Ltd.			
1:1	DWG NO.	型号:UK-B0206-G3.8-250-JZ	SIZE A4
1 of 1	PART NO.	规格: 4.5*4.5*3.8 贴片	VER R