




P.C.B LAYOUT TOP VIEW



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature: -20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

②	Terminal	5	Phosphor bronze	Au Plating		
①	Housing	1	Nylon	Black		
ITEM	PART NAME	TERNNO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS		DATE				
DRAWN		JIANKUNLIU		2015.4.14		
CHECKED				TITLE: PHONE JACKES		
APPROVALS				PART NO. PJ-242		
TOLERANCES ARE		30 ^{±0.15}	±0.30	ANGLE	SCALE: 1:1	
		10 ^{±0.10}	±0.20	UNIT: mm	PROJ.	
		5 ^{±0.10}	±0.15	±Z'	DRAWING NO.	
		~ 5	±0.10		SHEET 1 OF 1	

HPRO
 ELECTRONICS CO.,LTD