



| 版次 (REV) | 变更编号 (ECN NO) | 说明 (DESCRIPTION) | 日期 (DATE) | 核准 (APPD) |
|----------|---------------|------------------|-----------|-----------|
| X1 | | 初版发行 | | |
| | | | | |



APPLICABLE FPC
RECOMMENDED DIM.
(THICKNESS: 0.3 ± 0.03)




旧料号

88065-XXX X X X
PIN数

电镀: 1镀金 2镀雾锡 3镀亮锡

包材: A管装 B袋装 C盒装 D卷装

| NO | 胶体 材质 | 锁扣 材质 | 胶体 颜色 | 锁扣 颜色 | 柱子 |
|----|----------|----------|----------|----------|----|
| 1 | LCP | LCP | 本色 | 黑色 | |
| 2 | PA9T | LCP | 本色 | 黑色 | |



新料号


1010A*-***-***

1:17P插8针 2:53P插26针
3:9P插4针 4:13P插6针

PIN数

1:LCP 2: PA9T
P:盘装 G:管装
1:雾锡2: 亮锡3: 镀金


| CKT | Dim A | Dim B | Dim C |
|-----|-------|-------|-------|
| 004 | 3.00 | 5.06 | 8.70 |
| 005 | 4.00 | 6.06 | 9.70 |
| 006 | 5.00 | 7.06 | 10.70 |
| 007 | 6.00 | 8.06 | 11.70 |
| 008 | 7.00 | 9.06 | 12.70 |
| 009 | 8.00 | 10.06 | 13.70 |
| 010 | 9.00 | 11.06 | 14.70 |
| 011 | 10.00 | 12.06 | 15.70 |
| 012 | 11.00 | 13.06 | 16.70 |
| 013 | 12.00 | 14.06 | 17.70 |
| 014 | 13.00 | 15.06 | 18.70 |
| 015 | 14.00 | 16.06 | 19.70 |
| 016 | 15.00 | 17.06 | 20.70 |
| 017 | 16.00 | 18.06 | 21.70 |
| 018 | 17.00 | 19.06 | 22.70 |
| 019 | 18.00 | 20.06 | 23.70 |
| 020 | 19.00 | 21.06 | 24.70 |
| 021 | 20.00 | 22.06 | 25.70 |
| 022 | 21.00 | 23.06 | 26.70 |
| 023 | 22.00 | 24.06 | 27.70 |
| 024 | 23.00 | 25.06 | 28.70 |
| 025 | 24.00 | 26.06 | 29.70 |
| 026 | 25.00 | 27.06 | 30.70 |
| 027 | 26.00 | 28.06 | 31.70 |
| 028 | 27.00 | 29.06 | 32.70 |
| 029 | 28.00 | 30.06 | 33.70 |
| 030 | 29.00 | 31.06 | 34.70 |



Solder Area
 No Pattern Area

Electrical

Voltage:50 V AC(rms)/DC
Current:0.5 A AC(rms)/DC
Contact Resistance:40 mΩ max(initial)
Dielectric Withstanding Voltage:200 V AC/rms
Insulation Resistance:800 MΩ min
Operating Temp:-25° C~+85° C



| | | | | | |
|---|--|-----------------|---|-----------------------------|-------------------|
| 使用类别 (EXTEND USE) 0.5mm掀盖 FPC H=2.0 **P插**针 | | | 品名 (TITLE) 0.5mm掀盖 FPC H=2.0 **P插**针 | 图号 (DWG NO): 1010A* | |
| 尺寸公差 DIMENSION ±0.30 .0 ±0.20 .00 ±0.10 .000 ±0.05 | | 单位 (UNIT) mm | 客户图面 | 料号 (P/N): 1010A*-***-*** | |
| 角度公差 ANGLES ±3° .0 ±2° .00 ±1° | | 原材料 (MATERIAL) | 核准 (APPD) | 审核 (CID) | |
| | | 数量 (QTY) | 审核 (CID) | 表面处理 (FINISHED) | |
| | | 表面处理 (FINISHED) | 绘图 (DRN) 尹彩艳 2010/5/19 | 页数 (SHEET) 1/1 | 比例 (SCALE) 1:1 |