



Poles: 2P&3P-24P
 Pitch: 6.35mm
 Voltage Rating: 300V
 Current Rating: 30A
 Wire range: 26-10AWG 4.0mm²
 Housing: PA66 (UL 94V-0)
 Wire Cage: Brass1, Nickel Plated
 Solder Pin: Brass, Tin Plated
 Screw: M3.0, Steel (A3), Zinc Plated
 Torque: 0.5N.m

序号/Rev.No. 更改记录/Revision note 签名/Signature 日期/Date

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance	
				x ±0.2	x ±2°
图名/Title	文件编号/File No.			.x ±0.1	.x° ±1°
XY636-6.35				.xx ±0.05	.xx° ±0.5°
备注/Remark	页序/Sheet			.xxx ±0.01	
				单位/Units:	mm


新莱亚电子
 XINLAIYA ELECTRONIC CO., LTD