



GENERAL TOLERANCES UNLESS SPECIFIED		PART NO. SEE TABLE	LOTES		
X ± 0.35	X.° ± 3°				
.XX ± 0.25	.X.° ± 2°		APPROVED BY Barney	TITLE 0.5 PITCH M.2 H2.3 (E key)	
.XXX ± 0.15	.XX.° ± 1°	CHECKED BY Vito	DWG NO. AP-APCI0147-P		
SIZE A4	UNITS MM [INCH]	DRAWN BY Jason	SHEET 2 / 4	SCALE 4 : 1	REV 1
CUSTOMER DRAWING					



GENERAL TOLERANCES UNLESS SPECIFIED		PART NO. SEE TABLE	LOTES		
X ± 0.35	X° ± 3°				
.XX ± 0.25	.X° ± 2°	APPROVED BY Barney	TITLE 0.5 PITCH M.2 H2.3 (E key)		
.XXX ± 0.15	.XX° ± 1°	CHECKED BY Vito	DWG NO. AP-APCI0147-P		
CUSTOMER DRAWING		DRAWN BY Jason	SHEET 3 / 4	SCALE 4 : 1	REV 1
SIZE A4	UNITS MM [INCH]				



1500	12000
PCS/REEL	PCS/CARTON

GENERAL TOLERANCES UNLESS SPECIFIED		PART NO. SEE TABLE	LOTES			
X ± 0.35	X° ± 3°					
.XX ± 0.25	.X° ± 2°	APPROVED BY Barney	TITLE 0.5 PITCH M.2 H2.3 (E key)			
.XXX ± 0.15	.XX° ± 1°	CHECKED BY Vito	DWG NO. AP-APCI0147-P			
CUSTOMER DRAWING		DRAWN BY Jason		SHEET	SCALE	REV
SIZE A4	UNITS MM [INCH]			4 / 4	1 : 1	1