



Poles: 2P&3P-24P
 Pitch: 6.35mm
 Voltage Rating: 300V
 Current Rating: 30A
 Wire range: 26-10AWG 4.0mm²
 Housing: PA66 (UL 94V-0)
 Wire Cage: Brass1, Nickel Plated
 Solder Pin: Brass, Tin Plated
 Screw: M3.0, Steel (A3), Zinc Plated
 Torque: 0.5N.m

序号/Rev.No. 更改记录/Revision note 签名/Signature 日期/Date

设计/Drawn by: 绘图/Drawn by: 审核/Checked by: 批准/Approved by: 未注公差/General Tolerance

图名/Title	文件编号/File No.	X	X	X	X
XY636-6.35		.X	.XX	.XXX	.XX
页序/Sheet		.00.2	.00.1	.00.05	.00.01

新莱亚电子
 XINLAIYA ELECTRONIC CO., LTD

备注/Remark: 单位/Units: mm