



300V 10A 22-14AWG 2.5mm<sup>2</sup>  
 Poles: 2P&3P-24P  
 Pitch: 5.0mm (.197")

**Materials**

Housing: PBT(UL 94-0)  
 Wire Protector: Stainless Steel  
 Solder Pin: Brass, Tin Plated  
 Screw: M3, Steel (A3), Zinc Plated  
 Torque: 0.5N.m

设计/Drawn by	绘图/Drawn by	审核/Checked by	批准/Approved by	备注/Remarks
-------------	-------------	---------------	----------------	------------

名称/Name	文件编号/File No.	规格/Spec.	公差/Tolerance
XY300VA-5.0			


**新莱亚电子**  
 XINLAIYA ELECTRONIC CO., LTD  
 单位/Unit: mm