



Poles: 2P&3P-24P  
 Pitch: 7.62mm  
 Voltage Rating: 300V  
 Current Rating: 30A  
 Wire range: 26-10AWG 4.0mm<sup>2</sup>  
 Housing: PA66 (UL 94V-0)  
 Wire Cage: Brass1, Nickel Plated  
 Solder Pin: Brass, Tin Plated  
 Screw: M3.0, Steel (A3), Zinc Plated  
 Torque: 0.5N.m

设计/Drawn by:	绘图/Drawn by:	审核/Checked by:	批准/Approved by:	未注公差 General Tolerance	
更改记录/Revision note	签名/Signature	日期/Date	图名/Title	文件编号/File No.	X <sup>+</sup> ±0.2 X <sup>+</sup> ±0.1 .XX ±0.05 .XXX ±0.01
			XY636-7.62	页序/Sheet	X <sup>+</sup> ±0.5 X <sup>+</sup> ±0.5 X <sup>+</sup> ±0.5
			备注/Remark	单位/Units:	mm



**新莱亚电子**  
 XINLEIYI ELECTRONIC CO., LTD