



■ Specifications :

- Voltage rating: 125V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥100MΩ
- Contact resistance: ≤20mΩ
- After environmental testing: ≤40mΩ

X1002 T- P XX-A
① ② ③ ④ ⑤

- ① Series No.
- ② Category : T-terminal
- ③ Material:P-Phosphor bronze
- ④ Plating Style:
V01-All Gold Flash
SN-Bright tin plating 70u";30u" Ni
SN2-50u" Ni Min,120u" Tin Min
- ⑤ Mold No./Mark/Special No. A-Ultra-thin

X1002T-PSN2-A	Phospho Bronze	AWG#26-32	0.92mm	Stamping Before Plating:50u" Ni;120u" Sn Min	X1002H-A ,X1002H-B
X1002T-PVD1-A				Stamping Before Plating:30u" Ni;100u" Gold;50u" Ni	
X1002T-PSN1-A				Stamping Before Plating:30u" Ni;120u" Sn	
PART No	Material	Wire Range	Insulation O.D.	Finish	Suitable XKB Terminal

					ANGLAR	±5°	DSND		DATE		SCALE: N/A	MODEL TYPE: X1002T-XXX-A		
ΔX						L ≤ 4	±0.2	DWN		DATE	VIEW:	PART NO.:		
ΔX						4 < L ≤ 16	±0.3	CHKD		DATE	UNIT: mm/in	1.0mm Crimp Style Connectors		
ΔX						16 < L ≤ 63	±0.4	APPD		DATE	SIZE: A4	DWG NO.:		
MARK	DESCRIPTION					L > 63	±0.5					WEIGHT	SHEET	REVISION
REVISIONS					UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO., LIMITED					1.0g	1/1	A0
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn														