





CUSTOMER DRAWING

焊脚尺寸以顺畅过孔规为准

版次 REV.	ECN编号 ECN NUMBER	设变内容 MODIFICATION	日期 DATE	制图 DRAW	核准 APPROVE
A		初版发行	18-JAN-18	DOREN	DDS
B		UPDATE	15-MAY-19	DOREN	DDS



PCB LAYOUT
TOL: ±0.05

NOTES

MATERIAL

- 1. HOUSING MATERIAL : GLASS FILLED POLYESTER UL94V-0.
- 2. CONTACT MATERIAL : PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
- 3. PLATING : SELECT GOLD PLATING OVER NICKEL 50u".
- 4. SHIELD : 0.20mm THICKNESS COPPER ALLOY WITH NICKEL 30u" PLATED.

ELECTRICAL

- 1. VOLTAGE RATING : 125 VAC RMS.
- 2. CURRENT RATING : 1.5 AMP.
- 3. CONTACT RESISTANCE : 40 MILLIOHMS MAX.
- 4. INSULATION RESISTANCE : 500 MEGOHMS MIN @ 100V DC .
- 5. DIELECTRIC DIELECTRIC RESISTANCE : 500V DC RMS 50Hz. 1MIN.

MECHANICAL

- 1. DURRABILITY : 750 CYCLES MIN.
- 2. MATING/UNMATING FORC : 2.24 KG. F MAX.

ENVIRONMENTAL:

- 1. STORAGE : -40°C ~ +85°C.
- 2. OPERATION : 0° C TO 70° C.

RJ 0 10 - ZZ X - 1 0 X - 002

系列码 无弹

塑胶码
0: PBT黑色
1: PBT黄色
2: PA46黑色

8P8C DIP
1: GOLD FLASH
3: 3u"

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GMA AND SHALL NOT BE REPRODUCED, COPIED OR IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GMA	DIMENSION IN mm [Inch]		GMA 东莞市国满电子科技有限公司 Dongguan Guoman Electronic Technology Co., Ltd.	
	TOLERANCE UNLESS OTHERWISE SPECIFIED		料号 FILE NO.	图号 DWG NO.
	.X ± 0.35	X° ± 3°	RJ010-ZZ1-10X-002	RJ002-Z1
	.XX ± 0.25	.X° ± 2°	名称 TITLE	
	.XXX ± 0.15	.XX° ± 1°	RJ45 56 B型无弹无灯DIP	
核准 APPROVE	审核 CHECK	制图 DRAW	角法 PROJ.	图纸 SIZE A4
ZILL	DDS	DOREN	比例 SCALE 1:1	张数 SHEET 1/1
			版次 REV B	