



PANEL CUT-OUT

Rating :

10A 250V AC T105 UL cUL
10A 250V AC VDE 3C KC

Insert And Extract Force: 1.36kgf~6.8kgf

Operating Life: ≥5000 cycles

Withstand Voltage: Between all terminals:2500VAC (50-60Hz)1min
terminals to Base:3750V AC (50-60Hz)1min
Leakage Current : 1mA

Insulation Resistance: ≥100MΩ 500V DC

Body Materil: PBT 94V-2~0

A4				普通公差	LECI 乐磁电子有限公司 LECI ELECTRONICS CO., LTD								
A3				COMMON TOLERANCE :									
A2				UP TO 5	±0.20	单位	mm	投影		品名	Ac Inlet C14型	比例	Free
A1				ABOVE 5 TO 30	±0.30	绘图		核对		型号	DB-14		
REV.	DATE	REVISION DESCRIPTION	ISSUE	ABOVE 30	±0.50	DRAWN BY		核准		料号	DB-14-F1		
				ANGULAR	±5°	日期		核准		PART NO.			