



PANEL CUT-OUT		
Z	Y	X
0.70~1.25	12.90~13.10	18.9~19.1
1.25~2.00	12.90~13.10	19.1~19.2
2.00~3.00	12.90~13.10	19.3~19.4

NOTES:

1. Rating:
CQC 6A 250VAC 6(8)A 250VAC
8A/128A 250VAC T105/55
UL CUL 10GPA 125VAC
6GPA 250VAC T105/55
VDE ENEC 6(4)A 250VAC T85/55
KC 6(4)A 250VAC T85/55
2. Circuit Diagram: 2P ON-OFF
3. Terminal Strength: $\geq 80N$
4. Electrical life: ≥ 10000 cycles
5. Withstand Voltage: Withstand Voltage: 1500VAC 1min
Terminals to Button: 3000VAC 1min
6. Leakage Current: 1mA
7. Current resistance: $\leq 50m\Omega$ (initial)
8. Insulation resistance: $\geq 100M\Omega$
9. Body Material: NYLON 66 94V-2~0

SWITCHING CIRCUIT



普通公差:

COMMON TOLERANCE:

UP TO 5	± 0.20
ABOVE 5 TO 30	± 0.30
ABOVE 30	± 0.50
ANGULAR	$\pm 5^\circ$

LECI

乐磁电子有限公司
LECI ELECTRONICS CO., LTD

单位	mm	投影	梁金勇	品名	跷板开关	比例	Free
UNIT		PROJECTED		PRODUCT NAME		SCALE	
绘图	周金勇	校对	梁金勇	型号			RS601
DRAWN BY		CHECKED BY		MODEL NO.			
日期	2015.10.15	核准	周培雷	图号			RS601-1010011BB
DATE		APPROVAL BY		DWG. NO.			

A4			
A3			
A2			
A1			
REV.	DATE	REVISION DESCRIPTION	ISSUE