

PANEL CUT-OUT		
Z	Y	X
0.70~1.25	13.10~13.20	18.9~19.1
1.25~2.00	13.10~13.20	19.1~19.2
2.00~3.00	13.10~13.20	19.3~19.4

NOTES:

1. Rating:

CQC 6A 250VAC 6(8)A 250VAC

8A/128A 250VAC T1105/55

UL cUL 6GPA 250VAC

10GPA 125VAC

T1105/55 TV-5

VDE ENEC 6(4)A 250VAC T85/55

KC 6(4)A 250VAC T85/55

TUV 8/128A 250VAC T85/55

2. Circuit Diagram: 4P ON-OFF

3. Terminal Strength: ≥80N

4. Electrical Life: ≥10000 cycles

5. Withstand Voltage: Withstand Voltage: 1500VAC 1min



Terminals to Button: 3000VAC 1min

Leakage Current: 1mA

6. Current resistance: ≤50mΩ (initial)

7. Insulation resistance: ≥100MΩ

8. Body Material: NYLON 66 94V-0-2



LECI

乐磁电子有限公司
LECI ELECTRONICS CO., LTD

普通公差:

COMMON TOLERANCE:

UP TO 5 ±0.20

ABOVE 5 TO 30 ±0.30

ABOVE 30 ±0.50

ANGULAR ±5°

单位 mm
绘图 周金勇
日期 2015.9.1

投影 梁金勇
核校 周培雷
日期 2015.9.1

品名 跷板开关
型号 RS601D
图号

比例 1:1
图号 RS601D-2010011BB

A4
A3
A2
A1
REV.

DATE
REVISION DESCRIPTION
ISSUE