

PANEL CUT-OUT		
Z	Y	X
0.70~1.25	12.90~13.10	18.9~19.1
1.25~2.00	12.90~13.10	19.1~19.2
2.00~3.00	12.90~13.10	19.3~19.4

NOTES:

1. Rating:

CQC 6A 250VAC 6(8)A 250VAC

8A/128A 250VAC T105/55

UL cUL 6GPA 250VAC

10GPA 125VAC

T105/55 TV-5

VDE ENEC 6(4)A 250VAC T85/55

KC 6(4)A 250VAC T85/55

TUV 8/128A 250VAC T85/55

2. Circuit Diagram: 4P ON-OFF

3. Terminal Strength: ≥80N

4. Electrical life: ≥10000 cycles

5. Withstand Voltage: Withstand Voltage: 1500VAC 1min



Terminals to Button: 3000VAC 1min

Leakage Current: 1mA

6. Current resistance: ≤50mΩ (initial)

7. Insulation resistance: ≥100MΩ

8. Body Material: NYLON 66 94V-0~2



**LECI**

乐磁电子有限公司  
LECI ELECTRONICS CO., LTD

普通公差:

COMMON TOLERANCE:

UP TO 5 ±0.20

ABOVE 5 TO 30 ±0.30

ABOVE 30 ±0.50

ANGULAR ±5°

REV.	DATE	REVISION DESCRIPTION	ISSUE	单位	mm	投影	核	图	图	图	图	图
REV.	DATE	REVISION DESCRIPTION	ISSUE	UNIT	mm	PROJECTED	CHECKED BY	DRAWN BY	DATE	APPROVAL BY	DATE	DATE
A4												
A3												
A2												
A1												

RS601D-201N011RB