


PANEL CUT-OUT		
Z	Y	X
0.70~1.25	9.00~9.10	13.50~13.60
1.25~2.00	9.00~9.10	13.60~13.70

- NOTES:
1. Rating: VDE ENEC 3A 250VAC T125/55
UL cUL 6GPA 125VAC/3GPA 250VAC T105/55
CQC 3A 250VAC, 3A/40A 250VAC T105/55
 2. Circuit Diagram: 2P ON-OFF
 3. Terminal Strength: $\geq 40N$
 4. Electrical life: ≥ 10000 cycles
 5. Withstand Voltage: 1500VAC 1min
Terminals to Button: 3000VAC 1min
Leakage Current: 1mA
 6. Current resistance: $\leq 50m\Omega$ (initial)
 7. Insulation resistance: $\geq 100M\Omega$
 8. Body Material: NYLON 66 94V-0~2



普通公差:
COMMON TOLERANCE:

UP TO 5	±0.20
ABOVE 5 TO 30	±0.30
ABOVE 30	±0.50
ANGULAR	±5°

LECI 乐磁电子有限公司

LECI ELECTRONICS CO., LTD

单位	mm	投影	梁金勇	产品名称	跷板开关	比例	Free
绘图	周金勇	核对	梁金勇	型号	RS601H		
日期	2015.09.19	核准	周培雷	图号	RS601H-1010011BB		

A4			
A3			
A2			
A1			
REV.	DATE	REVISION DESCRIPTION	ISSUE