





REV	ECN NO.	APPD
A	HC-14-0028	PROLOM
B	HC-15-0056	PROLOM



规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V (50~60Hz) 60S min.
操作力 Operation force	≤ 180±30gf ≥ 250±50gf
寿命试验 Operating life	100,000cycles 100,000cycles
行程 Travels	看左侧编号说明



PRODUCT NO.: 1TS009*****-CT

- 轻触开关 TMRV 系列
- 外形: A=弧盖弯脚 B=平盖弯脚 C=弧盖平脚 D=平盖平脚
- 按钮颜色: 底座颜色: 盖板颜色: 操作力度: 手感: 材质: 产品高度 (H):
- 初始颜色 则不启用
- 非编带, 不启用

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	COVER	1	LCP	BLACK
4	ACTUATOR	1	SILICONE	/
3	CONTACT	1	STAINLESS STEEL	Ag-PLATED
2	TERMINAL	2	BRASS	Ag-PLATED
1	HOUSING	1	LCP	BLACK

X. ± 0.3	X' ± 3'	UNITS	MM	NAME (INTENDED USE)	TMRV SERIES TACT SWITCH	HON YUAN HON YUAN PRECISION IND. CO., LTD. SHENZHEN, CHINA, R.O.C.
.X ± 0.2	.X' ± 2'	MAT'L		PART NO. (INTENDED USE)	1TS009C-****-****	PRODUCT DRAWING
XX ± 0.1	.XX' ± 1'	FINISH		APPD:		DWG NO.: 1TS009C
.XXX ± 0.05	.XXX' ± 0.5'			CHKD:		SCALE SHEET REV. 10/1 1/1 B

DR: Y.Y.Chen 2015-11-10

10/1 1/1 B