



P.C.B Layout (copper-sided view)



Rating:0.5A 30V DC  
 Contact Resistance:100 mΩ Max.  
 Operating temperature:-20℃~70℃  
 Operating force:3-20N  
 Operating Life:5,000cycles

Model NO	A=φ6	PJ-3112A
	A=φ6	PJ-3112B
	A=φ7.3	PJ-3112C
	A=M6XP0.5	PJ-3112D
Schematic		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.																																																																							
	A		NEW																																																																										
<table border="1"> <tr> <td>② Terminal</td> <td>3</td> <td>Phosphor bronze</td> <td>Au Plating</td> </tr> <tr> <td>① Housing</td> <td>1</td> <td>Nylon</td> <td>Black</td> </tr> <tr> <td>ITEM</td> <td>PART NAME</td> <td>TER'NO.</td> <td>QTY.</td> <td>MATERIAL</td> <td>FINISHING</td> <td>REMARK</td> </tr> <tr> <td colspan="2">APPROVALS</td> <td>DATE</td> <td colspan="4"></td> </tr> <tr> <td>DRAWN</td> <td>J.X.Zhang</td> <td>2013/11/11</td> <td colspan="4"></td> </tr> <tr> <td colspan="3">CHECKED</td> <td colspan="4">TITLE: PHONE JACKES</td> </tr> <tr> <td colspan="3">APPROVALS</td> <td colspan="4">PART NO. PJ-3112A</td> </tr> <tr> <td colspan="3">TOLERANCES ARE</td> <td colspan="4">SCALE: 1:1</td> </tr> <tr> <td>10~30</td> <td>±0.30</td> <td>ANGLE</td> <td colspan="4">PROJ.</td> </tr> <tr> <td>5~10</td> <td>±0.15</td> <td>±2°</td> <td colspan="4">DRAWING NO.</td> </tr> <tr> <td>~5</td> <td>±0.10</td> <td></td> <td colspan="4">SHEET 1 OF 1</td> </tr> </table>							② Terminal	3	Phosphor bronze	Au Plating	① Housing	1	Nylon	Black	ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK	APPROVALS		DATE					DRAWN	J.X.Zhang	2013/11/11					CHECKED			TITLE: PHONE JACKES				APPROVALS			PART NO. PJ-3112A				TOLERANCES ARE			SCALE: 1:1				10~30	±0.30	ANGLE	PROJ.				5~10	±0.15	±2°	DRAWING NO.				~5	±0.10		SHEET 1 OF 1			
② Terminal	3	Phosphor bronze	Au Plating																																																																										
① Housing	1	Nylon	Black																																																																										
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK																																																																							
APPROVALS		DATE																																																																											
DRAWN	J.X.Zhang	2013/11/11																																																																											
CHECKED			TITLE: PHONE JACKES																																																																										
APPROVALS			PART NO. PJ-3112A																																																																										
TOLERANCES ARE			SCALE: 1:1																																																																										
10~30	±0.30	ANGLE	PROJ.																																																																										
5~10	±0.15	±2°	DRAWING NO.																																																																										
~5	±0.10		SHEET 1 OF 1																																																																										
<p><b>HAPO</b>                  ELECTRONICS CO.,LTD</p>																																																																													