



- Typical Specifications
1. Rating : DC 30V 0.3A
  2. Operating Force : 250 ± 50 gf
  3. Contact Resistance : 100mΩMAX
  4. Life : 100,000 Cycles Min

②	Terminal	4	Phosphor bronze	Au Plating	
①	Housing	1	Nylon	Black	
ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING
APPROVALS		DATE			
DRAWN		J.X.Zhang	2018/08/01		
CHECKED					
APPROVALS		TITLE: LED Tact Switch			
TOLERANCES ARE		30~φ以上 ±0.30	±0.20	ANGLE	PART NO. K6-6279D
		10~30 ±0.20	±0.15	UNIT: mm	SCALE: 1:1
		5~10 ±0.15	±0.10	DRAWING NO.	PROJ: 100
		~5 ±0.10			SHEET 1 OF 1



ELECTRONICS CO.,LTD

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			