


Kinghelm®

100±5mm



同向

- NOTES:
- ELECTRICAL:
 - VOLTAGE RATING: 60V AC RMS.
 - FREQUENCY RANGE: DC-3GHz
 - VSWR: 1.3 MAX.
 - CHARACTERISTIC IMPEDANCE: 50 OHMS
 - MATERIAL SEE TABLE:
 - ALL COMPONENTS ARE ROHS COMPLIANT.

REVISIONS				
REV NUMBER	DESCRIPTION	DWN	CHK	DATE
A	DESIGN			

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
②	端子	高仿 0.81 3代端子, 镀金	2
①	线材	0.81 黑色同轴线, OD:0.81	AS

深圳市金航标电子有限公司		WWW.BDS666.COM	
型号: KH-081-TX100-IPEX3		0755-83044319	
ALL DIMENSION ARE IN MM	DRAWN: Jamy	DATE	2018 /06/22
ENG: Ellis	MFG: Align	2018 /06/22	
COMPUTER GENERATED DO NOT SCALE THIS DRAWING	Q.A. Jeff	2018 /06/22	
PROJECTION	GENERAL TOLERANCE FOR ANGLES X.X XXX X.XXX ±1° ±0.3 ±0.25 ±0.150	SIZE Number	REV A
		SCALE: Free	SHEET OF 1

CUSTOMER P/N:

A

B

C

D

4

3

2

1

4

3

2

1

A

B

C

D