



Performance parameters	
Product name	WIFI Antenna
Model Type	KH-4G-SMA-108
Frequency Range	800-2700MHZ
V <sub>swr</sub>	≤3.0
Gain	2DBI
Impedance	50 Ω
Polarization	Vertical
Radiation	OMNIDIRECTIONAL
Max power	10 W
Connector	SMAJ
Dimensions	108mm*10mm
Shell material	ABS
Installation	screw
Temperature	-35° -- 75°
Weight	10 ± 3g

Autodesk

Autodesk

深圳市金航标电子有限公司

DWN BY/DATE JIANG 16-10-29	DESG BY/DATE	TOLERANCE .X± .XX± .XXX± ANGLES±	SCALE 1 : 1		ENG PROJECT NO. YG1610291102	型号:KH-4G-SMA-108	
CHK BY/DATE	APPD BY/DATE		UNIT m / m	SH 1 OF 1	CONTROL NO. YG-HD06	DWG NO.	REV