


Kinghelm®

REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			



三個配件出貨時另外附配件出貨(防水圈, 華司, 螺母)

NOTES:

1. ELECTRICAL:
 - 1.1. VOLTAGE RATING:DCV 300V 10MS
 - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
 - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
 - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
 - 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
4	套管	黑色热缩套管, OD:2.0MM	AS
3	端子	高仿I-PEX ,1.13端子, 镀金	1
2	接头	SMA防水母头母针, 分体, 11牙, 镀金	1
1	同轴线	RF 1.13灰色线,OD:1.13mm	AS

深圳市金航标电子有限公司 WWW.BDS666.COM
 型号: KH-FS90-SMA11L 0755-83044319

ALL DIMENSION ARE IN MM	DRAWN Jamy	DATE 2018 /09 /24	I-PEX 1.13 TO SMA 11牙防水母头 L=90MM
COMPUTER GENERATED IN SOLIDWORKS	ENG.		
DO NOT SCALE THIS DRAWING	MFG.		
PROJECTION	Q.A.		SIZE Number
GENERAL TOLERANCE FOR ANGLES			REV A
± 1° ± 0.3 ± 0.25 ± 0.150			SCALE: Free
			TYPE
			SHEET 1 OF 1

CUSTOMER P/N:

立刻移除水印