




SPECIFICATIONS

Current rating: 2A AC/DC
 Voltage rating: 250V AC/DC
 Contact resistance: 20mΩ max.
 Withstand voltage: 800V AC/min
 Insulation resistance: 1000MΩ/min.
 Temperature range: -25°C~+85°C
 Applicable PC board thickness: 0.031"~0.063"(0.8~1.6)

Material:
 Part No: 2~15
 HOUSING: PA66, UL 94V-2



Poles	Part No.	Dimension mm	
		A	B
2	2001H-2P	2.00	5.80
3	2001H-3P	4.00	7.80
4	2001H-4P	6.00	9.80
5	2001H-5P	8.00	11.80
6	2001H-6P	10.00	13.80
7	2001H-7P	12.00	15.80
8	2001H-8P	14.00	17.80
9	2001H-9P	16.00	19.80
10	2001H-10P	18.00	21.80
11	2001H-11P	20.00	23.80
12	2001H-12P	22.00	25.80
13	2001H-13P	24.00	27.80
14	2001H-14P	26.00	29.80
15	2001H-15P	28.00	31.80

.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	TITLE: 2001H-XP			
CHECKED:	DATE:	CLIENT P/N /			
DRAM: LYF	DATE: 2008-04-07	UNIT	mm	SCALE	free
		FILE NO.	Chantv-2001-0003	REV.	A

深圳市矽科盟实业有限公司
 CHANKLEMENT INDUSTRY CO., LTD