


300V 20A 26-12AWG 2.5mm²
 Poles: 2P&3P-24P
 Pitch: 7.5mm (.295") / 7.62mm (.300")

Materials

Housing: PA66 (UL 94V-0)
 Wire Cage: Brass, Nickel Plated
 Solder Pin: Brass, Tin Plated
 Screw: M3, Steel (A3), Zinc Plated
 Torque: 0.5N.m

序号/Revno.	更改记录/Revision note	签名/Signature	日期/Date
-----------	--------------------	--------------	---------

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance
				X: ±0.2 .X: ±0.1 .XX: ±0.05 .XXX: ±0.01
 新莱亚电子 XINMAIYA ELECTRONIC CO., LTD		图名/Title	文件编号/FILE NO.	X: ±2° .X: ±1° .XX: ±1° .XXX: ±0.5°
		XV129VB-7.5	页序/Sheet	单位/Units: mm
		7.62		
备注/Remark				