




HSF

NOTES:

Current Rating: 1.75AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 5000MΩ Min
 Operation Temperature: -55°C to +125°C

Contact Material: Brass 
 Contact plating: Au Or Sn over Ni
 Insulator Material: LCP+30%G.F UL94V-0

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Ordering Information

3231-XX R XX B S T 1

- No. of Pins
 - 06 26
 - 08 30
 - 10 34
 - 14 40
 - 16 44
 - 20 50
 - 24
- Contact Plating
 - G0=Gold Flash
 - G3=10u"Gold
 - G4=15u"Gold
 - G5=30u"Gold
 - S0=Gold Flash/Tin
 - S3=10u"Gold/Tin
 - S4=15u"Gold/Tin
 - S5=30u"Gold/Tin
 - SN=Tin
- Insulator Color
 - B=Black
 - T=Tube
- Packaging
 - T=Tube

Item	Pitch	Mating
Standard	1.27	5232
Alternate		

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A1	2012/12/24	MODIFY THE NOTES:Phosphor Bronze → Brass	
A0	2012/09/28	NEW	

OPERATION	DRAW	DATE	SCALE	FIT
XX	JYHuang	2012/12/24	mm	1/1
XX	CHECK	DATE	SIZE	A4
XX	APPROVE	DATE	SHEET	1/1
Angle	± 3'		PROJ.	
DIM	TOL			

PART NO.	3231-XXXXXBST1
TITLE:	1.27 Bjector Header "S" Type 90°
Customer NO.	

WCON

Http: www.wcon.com

WCON-Dongguan
 Tel: +86 769 85358920
 Fax: +86 769 85358915
 E-mail: sales@wcon.com

WCON-Kunshan
 Tel: +86 512 57468408
 Fax: +86 512 57468468
 E-mail: sales@wcon.com